




- NOTES:
- 1. SUBSTRATE  
LAMINATED WRATTEN 2
  - 2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: NONE  
S2: NONE
  - 3. LAMINATION  
S1: CLEAR AR @ 400-700nm  
S2: NONE
  - 4. RoHS EXEMPT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                         | S1                   | S2                   |
|-------------------------|----------------------|----------------------|
| SHAPE                   | PLANO                | PLANO                |
| TRANSMISSION PERCENTAGE | 16%                  | 16%                  |
| COATING APERTURE        | N/A                  | N/A                  |
| BEVEL                   | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE  
PROJECTION

ALL DIMS IN      mm

 **Edmund Optics®**

|        |                                             |              |  |
|--------|---------------------------------------------|--------------|--|
| TITLE  | OD 0.8, 50 x 50mm, LAMINATED WRATTEN FILTER |              |  |
| DWG NO | 84055                                       | SHEET 1 OF 1 |  |