




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

| | VALUE |
|----------------------------|--------------------------------|
| OPTICAL DENSITY | ≥3.0 |
| CENTER WAVELENGTH (CWL) | 532 ±2 nm |
| FULL WIDTH HALF MAX (FWHM) | 10 ±2 nm |
| MINIMUM TRANSMISSION | ≥45 % |
| BLOCKING | 200 - 1200nm |
| SURFACE QUALITY | 80-50 |
| CONSTRUCTION | MOUNTED IN BLACK ANODIZED RING |
| COATING TYPE | TRADITIONAL COATED |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Ø50mm, 532nm x 10nm, MOUNTED
BANDPASS FILTER

DWG NO

86628

SHEET
1 OF 1