NOTES:

1. SUBSTRATE MATERIAL: N-BK7


- 2. ROHS COMPLIANT
- 3. SURFACE \$1 TO BE PARALLEL TO SURFACE \$2 TO WITHIN ≤ 3 ARCMIN
- 4. COATING (APPLY ACROSS CLEAR APERTURE)


\$1: 50% R ±5% @ 550nm 50% T ±5% @ 550nm

S2: AR R(avg) ≤1%, R(abs) ≤2% @ 700 - 1100nm



CUT WITH 0.25mm MAXIMUM EDGE CHIP





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2	
SHAPE	PLANO	PLANO	
ANGLE OF INCIDENCE	45°	45°	
SURFACE QUALITY	60-40	60-40	
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm	

	R	E	dmund	l Optics®)
_			50 5 /50 5 5		

THIRD ANGLE PROJECTION	ϕ	TITLE	50 x 50mm, 50 R/50 T, PLATE BEAMSPLIT	
ALL DIMS IN	mm	DWG NO	45855	SHEET 1 OF 1