NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. BEAM DEVIATION: ±3 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


\$1, \$2, \$3 & \$4: R(abs) <0.25% @ 850nm \$5: Tp/Ts >1000:1 @ 850nm TRANSMISSION >95% REFLECTION >99.5%

4. FINE GROUND SURFACE

5 elements to be cemented with norland optical adhesive 61

6. PROTECTIVE BEVEL AS NEEDED

7. MARK IDENTIFIES BEAMSPLITTER COATING RIGHT ANGLE PRISM



(R)

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

			_			Edmund Opti	CC®
	S1, S2, S3, S4	\$5					63
SHAPE	PLANO	PLANO			TITLE	15mm, 850nm, LASER LINE POLARIZING CUBE BEAMSPLITTER	
SURFACE FLATNESS	λ/4	λ/4					
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	90	90	ALL DIMS IN	mm	DWG NO	47049	SHEET 1 OF 1