

NOTES:




1. SUBSTRATE: FLOAT GLASS
2. WAVELENGTH RANGE: 350 - 2000nm

 FINE GRIND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE


5. ROHS COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

 <sup>®</sup> **Edmund Optics** <sup>®</sup>

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	51.5mm DIAMETER FLOAT GLASS WINDOW	
SHAPE	PLANO	PLANO			ALL DIMS IN	mm	DWG NO
SURFACE FLATNESS	4 - 6λ	4 - 6λ					
COATING APERTURE	UNCOATED	UNCOATED					