



NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. BEAM DEVIATION: ± 5 ARCMIN
- 3. ROHS COMPLIANT
- 4. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1 & S2: R(avg) >85% @ 400 - 700nm W/BLACK OVERPAINT
 - S3 & S4: R(avg) $\leq 0.4\%$ @ 425 - 675nm
 - S5: BLACK PAINT

5. FINE GRIND SURFACE

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
ANGLE TOL.	± 5 arcmin
SURFACE QUALITY	60-40
SURFACE FLATNESS	$\lambda/8$
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION		Edmund Optics®	
ALL DIMS IN		TITLE	5mm, VIS 0° COATED, PENTA PRISM
mm		DWG NO	48595
		SHEET 1 OF 1	