NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 50% R ±5% @ 550nm 50% T ±5% @ 550nm

S2: AR 1/4λ MgF2 @ 550nm







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

1 OF 1

REV. A	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE FLATNESS	4 - 6λ	4 - 6λ
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

			Edmund Option	S®
HIRD ANGLE - PROJECTION		TITLE	35 x 35mm, 50 R/50 T, PLATE BEAMSPLI	TTER
all DIMS IN	mm	DWG NO	45325	SHEET 1 OF