NOTES:

## 1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT

3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 40% R ±5% @ 550nm 60% T ±5% @ 550nm

S2: 1/4 WAVE MgF2 @ 550nm





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

\_\_\_\_\_

					Edmund Optics <sup>®</sup>	
REV. A	S1	\$2				
SHAPE	PLANO	PLANO			25 x 38mm, 40 R/60 T, PLATE BEAMSPLITTER	
SURFACE QUALITY	80-50	80-50		TITLE		
SURFACE FLATNESS	4 - 6λ	4 - 6λ				_
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN mm	DWG NO	46668 SHEE 1 OF	