

NOTES:



1. SUBSTRATE MATERIAL:
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: NIR I

R(avg) $\leq 0.5\%$ @ 600 - 1050nm


3. FINE GROUND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2					
SHAPE	CONVEX	PLANO	EFL	20	 Edmund Optics®		
RADIUS	10.34	∞	BFL	18.03			
SURFACE QUALITY	60-40	60-40			TITLE	10mm DIA X 20mm FL NIR I COATED, CYLINDER LENS	
CLEAR APERTURE	Ø9.00	Ø9.00					
COATING APERTURE	Ø9.00	Ø9.00					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	69707	SHEET 1 OF 1