



NOTES:

1. SUBSTRATE MATERIAL:
Fused Silica
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: UV Enhanced Aluminum
R(avg) >89% @ 250 - 450nm
R(avg) >85% @ 250 - 700nm
S2: NONE




 FINE GROUND SURFACE

4. PARALLELISM: 30 ARCSEC
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	20-10	N/A				
SURFACE FLATNESS	λ/10	COMMERICAL POLISH		TITLE	35mm Square UV Enhanced Aluminum Coated, λ/10 Mirror	
CLEAR APERTURE	90%	N/A				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
			ALL DIMS IN	mm	DWG NO	84424
						SHEET 1 OF 1