

NOTES:



- 1. SUBSTRATE MATERIAL:  
Fused Silica
- 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Silver  
R(avg) >98% @ 450 - 2000nm  
R(avg) >98% @ 2000 - 10,000nm  
S2: NONE

3. FINE GROUND SURFACE



4. PARALLELISM: 30 ARCSEC

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	20-10	N/A				
SURFACE FLATNESS	$\lambda/10$	COMMERICAL POLISH	TITLE35mm Diameter Silver Coated, $\lambda/10$ Mirror			
CLEAR APERTURE	90%	N/A				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO84443	SHEET1 OF 1