

NOTES:

1. SUBSTRATE MATERIAL:
Fused Silica



2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Silver
R(avg) >98% @ 450 - 2000nm
R(avg) >98% @ 2000 - 10,000nm
S2: NONE

 FINE GROUND SURFACE


4. PARALLELISM: 30 ARCSEC

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	20-10	N/A				
SURFACE FLATNESS	λ/10	COMMERICAL POLISH				
CLEAR APERTURE	90%	N/A				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
			THIRD ANGLE PROJECTION 	TITLE	35mm Square Silver Coated, λ/10 Mirror	
			ALL DIMS IN mm	DWG NO	84444	SHEET 1 OF 1

 **Edmund Optics®**