



NOTES:

1. SUBSTRATE MATERIAL:  
Fused Silica
2. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1: Enhanced Aluminum  
R(avg) >95% @ 450 - 650nm  
  
S2: NONE

 FINE GROUND SURFACE

4. PARALLELISM: 30 ARCSEC
5. RoHS COMPLIANT




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	N/A
SURFACE FLATNESS	$\lambda/10$	COMMERICAL POLISH
CLEAR APERTURE	90%	N/A
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION



TITLE

12.5mm Square Enhanced Aluminum  
Coated,  $\lambda/10$  Mirror


ALL DIMS IN

mm

DWG NO

84410

SHEET  
1 OF 1

 **Edmund Optics®**