



NOTES:

1. SUBSTRATE MATERIAL:
Fused Silica
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Enhanced Aluminum
R(avg) >95% @ 450 - 650nm


S2: NONE
3.

FINE GROUND SURFACE
4. PARALLELISM: 30 ARCSEC
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A | S1 | S2 | <div><div><div>EO[®]</div><div>Edmund Optics[®]</div></div></div> | | | |
|------------------|----------------------|----------------------|--|----|--------|--------------|
| SHAPE | PLANO | PLANO | <div>TITLE</div> 75mm Square Enhanced Aluminum Coated, λ/10 Mirror | | | |
| SURFACE QUALITY | 20-10 | N/A | | | | |
| SURFACE FLATNESS | λ/10 | COMMERICAL POLISH | <div>TITLE</div> 75mm Square Enhanced Aluminum Coated, λ/10 Mirror | | | |
| CLEAR APERTURE | 90% | N/A | | | | |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | ALL DIMS IN | mm | DWG NO | 84416 |
| | | | THIRD ANGLE PROJECTION  | | | SHEET 1 OF 1 |