


NOTES:

1. OPERATING VOLTAGE: 4.5V - 5.5V
2. ACTIVATION TIME: 30ms
DEACTIVATION TIME: 50ms
3. COIL RESISTANCE: 155ohm @ 25°C
COIL RESISTANCE TOLERANCE : ±10%
4. OPERATING TEMPERATURE: -20 to +70°C



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	C-MOUNT ELECTRICAL SHUTTER	
ALL DIMS IN	mm	DWG NO	87208	SHEET 1 OF 1