




NOTES:

- 1. SUBSTRATE:
Film
- 2. COATING (APPLY ACROSS COATING APERTURE)
TRANSMISSION : >89%
- 3. RETARDANCE: 1λ
- 4. PHASE SHIFT : 360°
- 5. HAZE: <0.4%
- 6. DESIGN WAVELENGTH:560nm
- 7. CONSTRUCTION: Polarizing Film
- 8. ROHS: COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	50 x 50mm, 1λ Retarder Film
ALL DIMS IN	mm	DWG NO	88257
			SHEET 1 OF 1