





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



|                                     |                                                                |
|-------------------------------------|----------------------------------------------------------------|
| CENTER WAVELENGTH CWL (nm)          | 405                                                            |
| BANDWIDTH (nm)                      | 1.5                                                            |
| OPTICAL DENSITY OD                  | ≥6.0                                                           |
| TRANSMISSION (%)                    | >90                                                            |
| SURFACE QUALITY                     | 60-40                                                          |
| ANGLE OF INCIDENCE (°)              | 0 ±2                                                           |
| DURABILITY (ENVIRONMENTAL)          | MIL-STD-810F Paragraphs 501.4, 502.4, AND 507.4                |
| DURABILITY (PHYSICAL)               | MIL-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, AND 4.5.5.3 |
| OD 5 BLOCKING WAVELENGTH RANGE (nm) | 353.5-401 & 409.1-495.3                                        |
| OD 6 BLOCKING WAVELENGTH RANGE (nm) | 372.6-398.9 & 411.1-445.5                                      |
| RoHS                                | COMPLIANT                                                      |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

|                                                                                                              |    |        |                                                       |                 |
|--------------------------------------------------------------------------------------------------------------|----|--------|-------------------------------------------------------|-----------------|
| THIRD ANGLE PROJECTION  |    | TITLE  | 405nm High Performance Laser Line Filter<br>25mm Dia. |                 |
| ALL DIMS IN                                                                                                  | mm | DWG NO | 12276                                                 | SHEET<br>1 OF 1 |