




NOTES:

- 1. SUBSTRATE: FLOAT GLASS
- 2. LINE PAIR PATTERN: 500lp/inch
- 3. PARALLELISM:  
LINE TO LINE:  $\leq 2$  ARCSEC  
PATTERN TO SUBSTRATE:  $\pm 1^\circ$
- 4. COATING:  
S1: VACUUM DEPOSITED CHROME, OD > 3.0  
REFLECTION: 50%  $\pm$  5% @ 550nm  
  
S2: NONE
- 5. RoHS: COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**


SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
SURFACE QUALITY	20-10
SURFACE FLATNESS	1λ
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION

ALL DIMS IN

mm

 **Edmund Optics®**

TITLE

4" x 4" (500 lp/inch), Ronchi Ruling

DWG NO

56624

SHEET

1 OF 1