

## NOTES:

- 1. SUBSTRATE: FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <5 ARCSEC
- 3. COATING (APPLY ACROSS COATING APERTURE):

S1 & S2: NIR II (750-1550nm) R(ABS) ≤1.5% @ 750 - 800nm R(ABS) ≤1.0% @ 800 - 1550nm R(AVG) ≤0.7% @ 750 - 1550nm

4. WAVELENGTH RANGE: 750 - 1550nm





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2			Edmund Optics®
SHAPE	PLANO	PLANO		W	
SURFACE QUALITY	20-10	20-10			25mm Dia., 2mm Thick, NIR II Coated λ/10
TRANSMITTED WAVEFRONT (P-V)	0.10 WAVE	0.10 WAVE	THIRD ANGLE PROJECTION	TITLE	Fused Silica Window
CLEAR APERTURE	Ø20.00	Ø20.00			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN mm	DWG NO	11901 SHEET 1 OF 1