





FOCAL LENGTH (EFL): 44,5 ±0,45
 BACK FOCAL LENGTH (BFL): 42,69

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE	
R	23±0,023 CX		GLASS N-BK7 517/642	R	∞ PL
Øe	11,7			Øe	11,7
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm
4/	-			4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)
6/	-			6/	-
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®	
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				12,7mm Dia, x 44,5mm FL, Uncoated, Plano-Convex Lens	
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO
			49845		SHEET SIZE A4
					SHEET 1 OF 1