


LEFT SURFACE			MATERIAL		RIGHT SURFACE		
R	3,4±0,003 CX		GLASS	N-LaSF9 850/322	R	∞ PL	
Øe	1,5				Øe	1,5	
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm	
4/	-				4/	52,94'	
5/	20 - 10 (MIL-PRF-13830B)				5/	20 - 10 (MIL-PRF-13830B)	
6/	-				6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	2,0mm Dia, x 4,0mm FL, VIS 0 Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				DWG NO	65283	SHEET SIZE A4	SHEET 1 OF 1
INDICATIONS IN ACCORDANCE WITH ISO 10110				ALL DIMS IN:	mm		