



LEFT SURFACE			MATERIAL		RIGHT SURFACE	
R	3,4±0,003 CX		GLASS	N-LaSF9 850/322	R	∞ PL
Øe	1,5				Øe	1,5
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm
4/	-				4/	52,94'
5/	20 - 10 (MIL-PRF-13830B)				5/	20 - 10 (MIL-PRF-13830B)
6/	-				6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	2,0mm Dia, x 4,0mm FL, NIR I Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	65309	SHEET SIZE A4	SHEET 1 OF 1