

FOCAL LENGTH (EFL): 60 ± 0,6

BACK FOCAL LENGTH (BFL): 57,03

- 1 AR COATING: NIR II  
R(ABS) ≤ 1,5% FROM 750-800nm @ 0° AOI  
R(ABS) ≤ 1,0% FROM 800-1550nm @ 0° AOI  
R(AVG) ≤ 0,7% FROM 750-1550nm @ 0° AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	31,01±0,031 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	19		Øe	19
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT    SCALE: NONE    λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

20,0mm Dia, x 60,0mm FL, NIR II, Inked, Plano-Convex Lens

DWG NO

675371NK

SHEET SIZE  
A4

SHEET  
1 OF 1