




NOTES:

1. MATERIAL:
HOUSING: STAINLESS STEEL
LENS: D-ZK3
2. COATING (APPLY ACROSS CLEAR APERTURE)
R(AVG) <0.4% @ 350 - 600nm
3. CLEAR APERTURE: 5.00 mm
4. RoHS: COMPLIANT



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

| | | | | |
|------------------------|----|--------|--|-----------------|
| THIRD ANGLE PROJECTION | | TITLE | 543nm Alignment, 0.16 NA Fiber Collimator w/ FC Connector | |
| ALL DIMS IN | mm | DWG NO | 47224 | SHEET 1 OF 1 |