NOTES:

1. MATERIAL: HOUSING: STAINLESS STEEL LENS: D-ZLaF52LA

- 2. COATING (APPLY ACROSS CLEAR APERTURE) R(AVG) <0.4% @ 350 - 600nm
- 3. CLEAR APERTURE: 4.95 mm

FOR INFORMATION


PARTS TO THIS DRAWING


N

OT

D

4. RoHS: COMPLIANT






ON

TURE

FΔC



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

