



PART	PART #	MATERIAL
①	#63-457	Hoya ND-50
②	#55-246	Anodized Aluminum

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY


	FILTER SPECIFICATIONS
CLEAR APERTURE (mm)	> Ø11.00
TRANSMISSION	T (AVG) > 63% @ 400 - 700 nm
OPTICAL DENSITY	0.2 ±0.04
SURFACE QUALITY	80-50



Edmund Optics®

0.2 OD, 12mm CA, C-Mount Absorptive ND Filter

THIRD ANGLE PROJECTION



ALL DIMS IN

mm

TITLE

DWG NO

12933

SHEET 1 OF 1