




- NOTES:
- 1. MATERIAL:
BOROSILICATE GLASS CONTAINING ELONGATED SILVER CRYSTALS
 - 2. COATING SPECIFICATION:
S1 & S2: BBAR COATING
R(AVG) < 0.4% @ 960 - 1160nm @ 0° AOI
 - 3. EXTINCTION RATIO: >10,000:1
 - 4. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	5 x 5mm, 1060nm, Corning Polarcor™ Glass Polarizer	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	40-20	40-20					
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	13620	SHEET 1 OF 1