

TECHSPEC® TitanTL™

TELECENTRIC LENSES

#34-037 • f/16.0

TECHSPEC® TitanTL™ Telecentric Lenses are designed for machine vision systems and metrology applications that require a large field of view. These lenses feature large maximum sensor formats, a variety of working distance and magnification options, and a rear filter holder on the back of the lenses to allow for easy filter integration. On our 118mm, 182mm and 242mm FOV versions, the integrated mounting flange allows for ease of securing each lens without requiring an additional mount and provides an easy to locate reference plane.



Primary Magnification:	0.238X
Working Distance¹:	267mm
Depth of Field²:	±14.6mm (20% @ 20 lp/mm, f/16)
Max. Sensor Format:	35mm
Camera Mount:	M58 x 0.75
Aperture (f/#):	f/16
Distortion %:	<0.178%
Object Space NA:	0.0074

1. From front housing 2. Image space MTF contrast

Telecentricity:	<0.1°
Type:	Telecentric Lens
Length:	500.94mm
Front Diameter:	208mm
Weight:	7.441kg
RoHS:	Compliant
Number of Elements (Groups):	7 (5)
AR Coating:	MgF ₂ (400-700nm)

At 267mm W.D.												
Sensor Size	1/4"	1/3"	1/2.5"	1/2"	1/1.8"	2/3"	1"	1.1"	4/3"	APS-C	APS-H	35mm
Field Of View ³	15.1mm	20.2mm	24.4mm	26.9mm	30.3mm	37.0mm	53.8mm	59.7mm	72.7mm	94.2mm	122.7mm	151.3mm

3. Horizontal FOV on Standard (4:3) sensor format.




Figure 1: Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




Figure 2: Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

MTF & DOF: f/16.0

WD: 267mm

HORIZONTAL FOV: 151.3mm




Figure 3: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by f/#-defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 4: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.