


Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


400nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


400nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


425nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


425nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


450nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


450nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


475nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


475nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


500nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


500nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


525nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


525nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


550nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


550nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


575nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


575nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


600nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

600nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


625nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


625nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


650nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


650nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


675nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


675nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

700nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

700nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY

