




NOTES:

1. CONSTRUCTION: BLACK ANODIZED ALUMINUM
2. TECHNOLOGY: Hexa-Black™
3. ABSORBANCE (%): 99.9
4. WAVELENGTH RANGE (nm): 200 - 5,000

HEXA-BLACK STRUCTURE
FOR REFERENCE



INSIDE OF EXTENSION TUBE
IS COVERED IN HEXA-BLACK



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® **Edmund Optics**®

THIRD ANGLE PROJECTION		TITLE	10mm Length, Acktar Hexa-Black™ C-Mount Noise Reduction Extension Tube	
ALL DIMS IN	mm	DWG NO	15480	SHEET 1 OF 1