

NOTES:

- SUBSTRATE:
LIBA 2000+
- CENTERING TOLERANCE (AT 587.6nm): BEAM DEVIATION (HALF ANGLE): <25 ARCMIN
- COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: 1/4 WAVE MgF2 @ 550nm
R(AVG) < 1.75% FROM 400-700nm (N-BK7)

4. EDGE: AS MOLDED



5. ASPHERIC SURFACE DESCRIBED BY THE FOLLOWING EQUATION AND COEFFICIENTS SHOWN
IN TABLE BELOW

$$Z(Y) = \frac{\left(\frac{1}{\text{RADIUS}}\right) * Y^2}{1 + \sqrt{1 - (1+k) * \left(\frac{1}{\text{RADIUS}}\right)^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14} + M * Y^{16}$$


6. RoHS: COMPLIANT

COEFFICIENT TABLE 5.

	S1
Semi-diameter	10.0
Coefficient (1/RADIUS)	1.198633E-01
k	-9.668032E-01
D	0.000000E+00
E	9.699449E-05
F	2.662297E-07
G	1.429249E-09
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00
M	0.000000E+00



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL: 16.00	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL: 9.13			
RADIUS	8.343	∞		TITLE	LENS CONDENSER 20mm X 16mm MgF2 TS	
SURFACE QUALITY	As Molded	As Molded				
CLEAR APERTURE	Ø 17.77	Ø 17.77	ALL DIMS IN	mm	DWG NO	15193
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				SHEET 1 OF 1