




NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO < 1ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)  
S1 & S2: R(AVG) ≤0.4% @ 425 - 675nm


4. FINE GRIND SURFACE

- 5. RoHS COMPLIANT
- 6. SURFACE FLATNESS (P-V): λ/4 (per inch over clear aperture)



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                     |  |                      |                      |                                                                                       |             |    |                                                                                                      |  |
|---------------------|--|----------------------|----------------------|---------------------------------------------------------------------------------------|-------------|----|------------------------------------------------------------------------------------------------------|--|
|                     |  | S1                   | S2                   |                                                                                       |             |    |  Edmund Optics® |  |
| SHAPE               |  | PLANO                | PLANO                |  | TITLE       |    | 50.8mm DIA., 4mm THICK, VIS 0° COATED<br>λ/4 N-BK7 WINDOW                                            |  |
| SURFACE QUALITY     |  | 60-40                | 60-40                |                                                                                       | DWG NO      |    | 15434                                                                                                |  |
| CLEAR APERTURE (mm) |  | Ø45.72               | Ø45.72               |                                                                                       |             |    | SHEET 1 OF 1                                                                                         |  |
| BEVEL               |  | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |                                                                                       | ALL DIMS IN | mm |                                                                                                      |  |