
NOTES:


1. SUBSTRATE: N-BK7


- 2. S2 TO BE PARALLEL WITH S1 TO < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: R(AVG) < 0.5% @ 350 - 700nm



5. Rohs Compliant







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2		
SHAPE	PLANO	PLANO		
SURFACE QUALITY	60-40	60-40		
CLEAR APERTURE	Ø45.00	Ø45.00		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		

_				Edmund Optics®		
	THIRD ANGLE PROJECTION	\rightarrow	TITLE	50mm DIA., 6mm THICK, VIS-EXT COATED, λ/4 N-BK7 WINDOW		
	ALL DIMS IN	mm	DWG NO	13306	SHEET 1 OF 1	