

NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO < 1ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(ABS) <0.25% @ 532nm R(ABS) <0.25% @ 1064nm R(AVG) <1.0% @ 500 - 1100nm



5. Rohs Compliant





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE QUALITY	60-40	60-40			
CLEAR APERTURE (mm)	Ø22.86	Ø22.86			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			

				Edmund Optics		
	THIRD ANGLE PROJECTION	$\phi \lhd$	TITLE	25.4mm DIA., 2mm THICK, YAG-BB, COATED, λ/4 N-BK7 WINDOW	AR	
D	ALL DIMS IN	mm	DWG NO	15792	SHEET 1 OF 1	

