


NOTES:


- 1. SUBSTRATE: POLYMER FILM WP140HE
- 2. TRANSMISSION (%): >89
- 3. RETARDANCE: $\lambda/4$
- 4. PHASE SHIFT : 90°
- 5. HAZE: <1%
- 6. WAVELENGTH RANGE: 450 - 650 nm
- 7. CONSTRUCTION: POLARIZING FILM
- 8. ROHS: COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	300 x 300mm, $\lambda/4$ RETARDER FILM (WP140HE)	
ALL DIMS IN	mm	DWG NO	14725	SHEET 1 OF 1