NOTES:

MATERIAL

HOUSING: STAINLESS STEEL

LENS: D-ZK3


2. COATING


\$1 & \$2: R(ABS) <1.0% @ 600 - 1050nm


3. CLEAR APERTURE: 5.50mm

4. ALIGNMENT WAVELENGTH: 633nm

5. Rohs: Compliant







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

		B	Edmund Optics ®
THIRD ANGLE _ PROJECTION	ϕ	TITLE	LightPath 354220 633nm Alignment, 0.25 NA Fiber Collimator w/ FC/APC Connector

ALL DIMS IN mm DWG NO 16706 SHEET 1 OF 1