



NOTES:

1. SUBSTRATE: FUSED SILICA
2. RoHS: COMPLIANT
3. COATING (APPLY ACROSS COATING APERTURE)
 S1: R(AVG) ≥98% @ 750 - 1100nm (0 - 45°, All Polarizations)
 R(AVG) ≥99% @ 750 - 110nm (0 - 45°, S-Polarization)
 S2 & S3: NONE

4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	S3
SHAPE	PLANO	PLANO	PLANO
SURFACE QUALITY	20-10	FINE GRIND	COMMERCIAL POLISH
CLEAR APERTURE	$\varnothing 22.50$	N/A	N/A
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN mm

EO® Edmund Optics®

TITLE

25mm Dia., NIR Broadband Dielectric, $\lambda/10$ Stemmed Mirror

DWG NO

16736

SHEET
1 OF 1