





NOTES:

1. SUBSTRATE: Hoya UV30N



LONGPASS FILTER



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
$\Delta\lambda$	<40
TH (%)	>85
CUT-ON WAVELENGTH (nm)	300±7
SURFACE QUALITY	60-40
WAVELENGTH	UV
BEVEL	PROTECTIVE AS NEEDED



ALL DIMS IN

mm



TITLE

Hoya UV30N (300nm), 50mm Dia., 2.5mm  
Thick, Colored Glass Longpass Filter

DWG NO

18804

SHEET  
1 OF 1