





NOTES:

- SUBSTRATE: Hoya UV30N



LONGPASS FILTER

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
$\Delta\lambda$	<40
TH (%)	>85
CUT-ON WAVELENGTH (nm)	$300 \pm 7$
SURFACE QUALITY	60-40
WAVELENGTH	UV
BEVEL	PROTECTIVE AS NEEDED



ALL DIMS IN

mm

**EO**® Edmund Optics®

TITLE

Hoya UV30N (300nm), 50.8mm Sq., 2.5mm  
Thick, Colored Glass Longpass Filter

DWG NO

18806

SHEET  
1 OF 1