


NOTES:

- 1. SUBSTRATE:
H-K51
- 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE
S2: NONE

- 3. CENTERING: ≤30 ARCMIN



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	PLANO
SURFACE QUALITY	80-50 (typical)	80-50 (typical)
CLEAR APERTURE	∅ 23.00	∅ 23.00
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

EFL @ 587.6nm	25
BFL @ 587.6nm	19.4
THIRD ANGLE PROJECTION	
ALL DIMS IN	mm

EO® **Edmund Optics**®

TITLE 25mm Dia. x 25mm FL, Aspheric Condenser Lens

DWG NO 19517 SHEET 1 OF 1