



- NOTES:
- 1. COATING:  
S1: LAMBERTIAN BLACK  
THICKNESS: 3-8 (µm)
  - 2. ABRASION RESISTANCE: MODERATE
  - 3. HUMIDITY RESISTANCE: MIL-C-48497A
  - 4. OPERATING TEMPERATURE (°C): -269 TO +380
  - 5. WAVELENGTH RANGE (µm): 0.3 - 10



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

THIRD ANGLE PROJECTION		TITLE	20 x 26cm Sheet of Lambertian Black Foil, No Adhesive	
ALL DIMS IN	mm	DWG NO	20010	SHEET 1 OF 1