


- NOTES:
- 1. COATING:
S1: LAMBERTIAN BLACK
THICKNESS: 3-8 (µm)
 - 2. ABRASION RESISTANCE: MODERATE
 - 3. HUMIDITY RESISTANCE: MIL-C-48497A
 - 4. OPERATING TEMPERATURE (°C): -50 TO +150
 - 5. WAVELENGTH RANGE (µm): 0.3 - 10



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	20 x 26cm Sheet of Lambertian Black Foil, Low Outgassing Adhesive	
ALL DIMS IN	mm	DWG NO	20012	SHEET 1 OF 1