




- NOTES:
- 1. COATING:
S1: SPECTRAL BLACK™
THICKNESS: 3 - 7 (µm)
 - 2. ABSORBANCE: 99.5 - 99.7 (0 - 10° AOI) %
 - 3. ABRASION RESISTANCE: MODERATE
 - 4. HUMIDITY RESISTANCE: MIL-C-48497A
 - 5. OPERATING TEMPERATURE (°C): -40 TO +150
 - 6. WAVELENGTH RANGE (µm): 0.3 - 14



DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	20 x 20cm Sheet of Spectral Black Foil, Low Outgassing Adhesive
ALL DIMS IN	mm	DWG NO	20063
			SHEET 1 OF 1