

NORLAND PRODUCTS INCORPORATED

2540 Route 130, Bldg 100, Cranbury, NJ 08512 Tel • 609-395-1966 Fax • 609-395-9006 Website: www.norlandproducts.com

Norland Optical Adhesive 63

Norland Optical Adhesive 63 ("NOA63") is a clear, colorless, liquid photopolymer that will cure when exposed to ultraviolet light. Since it is a one part system and 100% solids, it offers many advantages in bonding of optical elements where the bonding surface can be exposed to light. The use of NOA 63 eliminates premixing, drying or heat curing operations common to other optical adhesive systems. Curing time is remarkably fast, and is dependent upon the thickness applied and the amount of ultraviolet light energy available.

NOA 63 is recommended for the bonding of achromats, prisms and all other precision compound optics. The outstanding characteristics of the adhesive are its low fluorescence and its excellent transmission in the near UV range. After full cure, the adhesive has good transmission from 320 to 3,000 nanometers.

This adhesive is also suitable for bonding glass to metal. The high viscosity of NOA 63 allows it to be applied as a selfsupporting drop or bead along the edge of a precision component to bond it to the substrate. The adhesive cures well in thick sections and has low shrinkage and a slight resiliency to minimize strain.

NOA 63 is cured by ultraviolet light with maximum absorption in the range of 350 to 380 nanometers. The recommended energy required for full cure is 4.5 Joules/sq. cm of long wavelength UV light.

In most optical applications, curing is done in two steps. First a short exposure, or precure, is used. This cures the adhesive enough to allow it to be handled without disturbing the alignment and keeps the number of alignment fixtures to a minimum. At this time, parts can be inspected and excess adhesive can be cleaned up with an acetone or alcohol moistened cloth. Any rejected pieces are most easily separated at this stage. Cure is completed by exposure for the remainder of the cure time.

The NOA bond can be separated in chlorinated solvent such as methylene chloride. The bonded area must be soaked in the solvent and normally will separate overnight if only precured. Longer times may be necessary depending upon the extent of the cure and the size of the bond area.

The NOA 63 can withstand temperatures of 15 to 60° C when used to bond glass optics. In some cases temperatures to 90° C are possible when the adhesive is used as a film or coating. The latter would depend upon the application.

Typical Cure Times				
LIGHT SOURCE	FILM THICKNESS	PRECURE	FULL CURE	
100 Watt Mercury* Spot Lamp at 6 inches	1 mil	15 seconds	5 minutes	
	40 mils	60 seconds	20 minutes	
2-15 Watt Fluorescent* Black Lights at 3 inches	1 mil	60 seconds	20 minutes	
	40 mils	180 seconds	60 minutes	


Some of the light sources that can be used to cure the adhesive are sunlight, mercury lamps, and fluorescent blacklights.

*Distributed by Norland Products Inc.

Typical Properties of NOA 63			
Solids	100%		
Viscosity at 25° C	2000 cps		
Refractive Index of Cured Polymer	1.56		
Elongation at Failure	6%		
Modulus of Elasticity (psi)	240,000		
Tensile Strength (psi)	5,000		
Hardness - Shore D	90		

Shelf life of the liquid is at least 6 months from the date of shipment if stored in a cool ($5-22^{\circ}$ C), dark place in the original container. If refrigerated, allow the adhesive to come to room temperature prior to use.

Care should be taken in handling this material. The Material Safety Data Sheet should be read for this product as well as for any associated products such as alcohol, acetone or methylene chloride. Prolonged contact with skin should be avoided and affected areas should be thoroughly washed with copious amounts of soap and water. If the adhesive gets into eyes, flush with water for 15 minutes and seek medical attention. Use the material in a well ventilated area, otherwise a NIOSH approved organic vapor mask is recommended.



Spectral Transmission of NOA 63

The data contained in this technical data sheet is of a general nature and is based on laboratory test conditions. Norland Products does not warrant the data contained in this data sheet. Norland does not assume responsibility for test or performance results obtained by users. It is the users responsibility to determine the suitability for their product application, purposes and the suitability for use in the user's intended manufacturing apparatus and methods. The user should adopt such precautions and use guidelines as may be reasonably advisable or necessary for the protection of property and persons. Nothing in this technical data sheet shall act as a representation that the product use or application will not infringe a patent owned by someone other than Norland Products or act as a grant of a license under any Norland Products Inc patent. Norland Products recommends that each user test its proposed use and application before putting into production.