




NOTES:


- 1. SUBSTRATE: POLYMER FILM XP42HE-40
- 2. OPERATING TEMPERATURE: -40 TO +80
- 3. WAVELENGTH RANGE:400 - 700nm
- 4. POLARIZATION: >99.99
- 5. TRANSMISSION (%):
SINGLE: 42.6 ±2
PARALLEL: 36.4
CROSSED: <0.001
- 6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	100 x 100mm Linear Polarizing Film (XP42HE-40)	
ALL DIMS IN	mm	DWG NO	26727	SHEET 1 OF 1