




NOTES:


1. SUBSTRATE: POLYMER FILM XP42HE-40
2. OPERATING TEMPERATURE: -40 TO +80
3. WAVELENGTH RANGE: 400 - 700nm
4. POLARIZATION: >99.99
5. TRANSMISSION (%):
SINGLE: 42.6 ±2
PARALLEL: 36.4
CROSSED: <0.001
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	200 x 200mm Linear Polarizing Film (XP42HE-40)	
ALL DIMS IN	mm	DWG NO	26729	SHEET 1 OF 1