




NOTES:


- 1. CUT-ON WAVELENGTH: 700±14.0nm
- 2. BLOCKING RANGE: 589.1 - 675.7nm
- 3. TRANSMISSION RANGE: >85% @ 724.7 - 1100nm
- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	700nm 12.45mm, Ultra-Thin OD 4.0 Longpass Filter	
ALL DIMS IN	mm	DWG NO	29195	SHEET 9 OF 24