




NOTES:

- 1. SUBSTRATE: BOROFLOAT®
- 2. COATING (APPLY ACROSS CLEAR APERTURE):
S1 & S2: R(ABS) ≤2.5% @ 550nm
- 3. FINE GRIND SURFACE
- 4. ROHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE FLATNESS	4 - 6λ	4 - 6λ
SURFACE QUALITY	80 - 50	80 - 50
CLEAR APERTURE	Ø 27.00	Ø 27.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS INmm

 Edmund Optics®

TITLE

30mm Diameter x 1.1mm Thickness, MgF2
Coated, BOROFLOAT® Window

DWG NO

29404

SHEET
1 OF 1