





$f'$ :  $7 \pm 0,07$

BACK FOCAL LENGTH (BFL): 5,5



| LEFT SURFACE                                                                                                                                                                                                                                                                                                                                                          |                                                   |                                                  | MATERIAL                                                                             | RIGHT SURFACE                                                                                                                                                                                                                                                                                   |                |             |                                                                                                                                                                                                                                                                                                                                    |  |  |       |                                                   |  |        |       |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------|--------------------------------------------------|--------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|-------|---------------------------------------------------|--|--------|-------|
| <div>R 5,5 CX</div> <div>Øe 6,3</div> <div><math>\lambda</math> AR Rave(600nm - 1050nm, 0°) ≤ 0,50%</div> <div>3/ 3 (0,5) λ=632,8 nm</div> <div>4/ 3,82'</div> <div>5/ 40 - 20</div> <div>6/ -</div> <div></div>                                                                   |                                                   |                                                  | <div>GLASS</div> <div>N-SF11 785/258</div> <div>Nd: 1,785</div> <div>Vd: 25,68</div> | <div>R ∞ PL</div> <div>Øe 6,3</div> <div><math>\lambda</math> AR Rave(600nm - 1050nm, 0°) ≤ 0,50%</div> <div>3/ 3 (0,5) λ=632,8 nm</div> <div>4/ -</div> <div>5/ 40 - 20</div> <div>6/ -</div> <div></div> |                |             |                                                                                                                                                                                                                                                                                                                                    |  |  |       |                                                   |  |        |       |
| <div>PROTECTIVE CHAMFERS AS NEEDED</div> <table><tr><td>ROHS:<br/>COMPLIANT</td><td>SCALE:<br/>NONE</td><td>λ = 587,6nm</td></tr></table> <div>SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY</div> <div>FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING</div> <div>INDICATIONS IN ACCORDANCE WITH ISO 10110</div> |                                                   |                                                  |                                                                                      | ROHS:<br>COMPLIANT                                                                                                                                                                                                                                                                              | SCALE:<br>NONE | λ = 587,6nm | <div><div> Edmund Optics®</div><table><tr><td>TITLE</td><td colspan="2">7mm Dia x 7mm FL, NIR I Coated, Plano-Convex Lens</td></tr><tr><td>DWG NO</td><td>71295</td><td><div>SHEET SIZE A4</div><div>SHEET 1 OF 1</div></td></tr></table></div> |  |  | TITLE | 7mm Dia x 7mm FL, NIR I Coated, Plano-Convex Lens |  | DWG NO | 71295 |
| ROHS:<br>COMPLIANT                                                                                                                                                                                                                                                                                                                                                    | SCALE:<br>NONE                                    | λ = 587,6nm                                      |                                                                                      |                                                                                                                                                                                                                                                                                                 |                |             |                                                                                                                                                                                                                                                                                                                                    |  |  |       |                                                   |  |        |       |
| TITLE                                                                                                                                                                                                                                                                                                                                                                 | 7mm Dia x 7mm FL, NIR I Coated, Plano-Convex Lens |                                                  |                                                                                      |                                                                                                                                                                                                                                                                                                 |                |             |                                                                                                                                                                                                                                                                                                                                    |  |  |       |                                                   |  |        |       |
| DWG NO                                                                                                                                                                                                                                                                                                                                                                | 71295                                             | <div>SHEET SIZE A4</div> <div>SHEET 1 OF 1</div> |                                                                                      |                                                                                                                                                                                                                                                                                                 |                |             |                                                                                                                                                                                                                                                                                                                                    |  |  |       |                                                   |  |        |       |