

[Afficher tous les 28 produits de la même famille.](#)

0-80 x 3/8" SHCS, 50/Pack



Stock **#56-268** [CONTACT](#)

⊖ 1 ⊕ €24^{.50}

AJOUTER AU PANIER

| Prix sur Quantité | |
|-------------------|----------------------------------|
| Qté 1-9 | €24,50 prix unitaire |
| Qté 10-24 | €22,05 prix unitaire |
| Need More? | Demande de Devis |

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Conformité réglementaire

[Conforme](#)

RoHS 2015:

[Visionner](#)

Certificate of Conformance:

Description produit

- Idéal pour l'Utilisation avec Notre Equipement de Positionnement de Taille Impériale
- Large Sélection de Tailles Disponibles
- 50 Pièces par Paquet
- [Kit de Vis](#) Disponible
- [Clés Allène](#) Aussi Disponible

Socket head cap screws offer a reliable, high-strength solution for mounting and assembling optical components in precision systems. Manufactured from durable alloy steel, these screws feature a sleek, consistent design that is ideal for use in many environments. The hexagonal socket head design allows for easy installation in tight spaces using standard [Allen Wrenches](#), ensuring repeatable, secure fastening without damaging surrounding optics or mounts.

Available in English and Metric threading and a variety of hex key sizes, these cap screws are perfect for integration with optical breadboards, translation stages, and custom assemblies. Whether you're building a prototype or maintaining alignment-critical systems, these versatile fasteners offer dependable performance and easy compatibility with Edmund Optics' mechanical components.

FAQ(s)

What is a cap screw used for?

Capscrews are used to fasten components securely in optical systems, mounts, and mechanical assemblies where precision and durability are necessary.

What's the difference between a cap screw and a bolt?

A cap screw is designed to fit tightly into a tapped hole and often provides a cleaner, more secure fit than a standard bolt. Unlike bolts which are tightened using a nut, socket head cap screws have a hexagonal socket making it easy to secure using an Allen wrench.

What materials are these cap screws made of?

Edmund Optics' cap screws are typically manufactured from alloy steel for corrosion resistance and strength in lab or production environments.

Are socket head cap screws reusable?

Yes, if not damaged or over-torqued, they can be reused repeatedly. Always check thread integrity and apply proper torque when reassembling.

Informations techniques

| | Allen Wrench Stock No. | Allen Wrench Hex Key Size | For Socket Head Cap | For Socket Head Set | For Button Head Cap |
|---------|-------------------------|---------------------------|---------------------|---------------------|---------------------|
| English | #58-639 | 0.028" | N/A | #0 | N/A |
| | #58-638 | 0.035" | N/A | #2 | #0 |
| | #56-271 | 0.050" | #0 | #4 | #2 |
| | #58-637 | 1/16" | #1 | #6 | #3 & #4 |
| | #56-270 | 1/64" | #2 & #3 | #8 | #5 & #6 |
| | #55-188 | 3/32" | #4 & #5 | #10 | #8 |
| | #55-189 | 7/64" | #6 | N/A | N/A |
| | #03-662 | 1/8" | N/A | 1/4" | #10 |
| | #55-190 | 9/64" | #8 | N/A | N/A |
| | #55-191 | 5/32" | #10 & #12 | 5/16" | #12 & 1/4" |
| | #55-192 | 3/16" | 1/4" | 3/8" | 5/16" |
| Metric | #58-636 | 0.9mm | N/A | M2 | N/A |
| | #55-452 | 1.5mm | M1.6 & M2 | M3 | M2.5 |
| | #57-445 | 2mm | M2.5 & M2.6 | M4 | M3 |
| | #55-451 | 2.5mm | M3 | M5 | M4 |
| | #55-199 | 3mm | M4 | M6 | M5 |
| | #55-200 | 5mm | M6 | M10 | M8 |